

CamCleaner 300



Advantages

- Healthier employees
- Less cleaning
- Less asthma and allergy suffering
- Reduced environmental impact

Applications: Air purifier for all types of indoor environments, for example hospitals, hotels, offices, homes, schools, public environments and where high quality air purification is required.

Power supply: 200..240V

Filter: E11.

Installation: Floor or wall

Design: Stainless steel / white

Average air purification area: 35m²

Item no.	Item name	Dimensions (WxHxD) mm	Transport dimensions (WxHxD)mm	Weight kg	Filter included in standard version *
94000038	Stainless steel	280x665x210	285x670x215	11	E11
94000043	White	280x665x210	285x670x215	11	E11

* Other filter classes available on request

Exchange

Item no.	Item name	Dimensions (BxHxD) mm	Filter class compliant with EN1822	Number of filters per air purifier	Comments
	Main filter	PL50EAL (280x195x77-00)	E11	2	Standard
94000015	UK plug 230V				

* Other filter classes available on request

Operating specifications

Setting	Air flow m ³ /h	Energy consumption/W	Noise level dBa	System efficiency 0,3-0,4µm (%)
1	82	42	31	>95
2	119	49	35	>95
3	280	82	41	>95