



Product Information

ETX085x105-Ø12 NL110-Type A

EAN 4031582330984

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

| | |
|-----------------------|----------------|
| Wheel diameter | 85 mm |
| Width of Tread | 105 mm |
| Axle Hole Ø | 12 mm |
| Hub length | 110 mm |
| Temperature | - 20 / + 60 °C |
| Dynamic Load capacity | 1000 kg |
| Static Load capacity | 2000 kg |
| Hardness of tread | A 92 Shore |

