

FEATURES

- **Sintered Bronze Material:** Provides high durability and resistance to wear, ensuring long service life.
- **Flanged Design:** Facilitates easy installation and alignment, reducing assembly time.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying load conditions.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads, enhancing reliability.
- **0.37 in Bore Size:** Compatible with a wide range of shafts, offering versatility.
- **0.62 in Outside Diameter:** Compact size for easy integration into systems.
- **3/8 in Width:** Ensures a snug fit in tight spaces.

RS PRO 0.37 in Flanged Plain Bearing

RS Stock No: 528-910



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under varying loads. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for use in demanding industrial environments. Its compact design allows for easy integration into existing systems, providing a cost-effective solution for reducing friction and wear.

General Specifications

Bore Size	0.37 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.62 in
Width	3/8 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

