

SAKAP SAKDK4N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	End and partition plate for terminals, grey, Height: 59.5 mm, Width: 1.5 mm, V-O, PA 66/6
Order No.	2108110000
Type	SAKAP SAKDK4N
GTIN (EAN)	4050118456066
Qty.	20 items

SAKAP SAKDK4N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	52.85	Depth (inches)	2.0807 inch
Height	59.5 mm	Height (inches)	2.3425 inch
Width	1.5 mm	Width (inches)	0.0591 inch
Net weight	4.05 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66/6	Colour	grey
UL 94 flammability rating	V-0		

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		