



Features:

- Class I Switch Mode Power Supply
- Wall-mountable with hinged lid
- Resilient case with side entry knockouts
- Built in PSU trimmer for Voltage Regulation
- Internal On/Off switch for DC outputs
- Easy to install, operate & maintain
- Front mounted indicator for mains OK and DC OK status



Characteristics						
Part Number	T5849ST	T5850ST	T5851ST	T5852ST	T5853ST	T5854ST
No. of Output	4	4	9	9	18	18
Output Voltage	12Vdc					
Fuse Protection (P.T.C)	2A	2A	1.1A	2A	1.1A	2A
Total Current Rating	5A Max	10A Max	5A Max	10A Max	10A Max	20A Max
Current Min.	0A					
Total Power Rating	60W	120W	60W	120W	120W	240W
Input Voltage Range	100-240Vac	100-240Vac	100-240Vac	100-240Vac	100-240Vac	180-264Vac
Input Frequency	50-60Hz					
Efficiency	81%					
Inlet Style	Terminal Block - Unit required to be Earthed.					
Lid Type	Key Lock					
Protections	Overload and Over Voltage Protections					
Operating Temp.	-30C to 45C					
Operating Hum.	20% to 90%					
MTBF	50,000 Hours Approx.					
Safety	Withstand Voltage: I/P-O/P:3KVAC, I/P-FG;1.5KVAC, O/P-FG:0.5KVAC					
Dimensions	250 x 215 x 59mm	250 x 215 x 59mm	250 x 215 x 59mm	250 x 215 x 59mm	250 x 215 x 59mm	265 x 205 x 90mm
Weight	1.85Kg	1.88Kg	1.85Kg	1.88Kg	1.88Kg	2.77Kg