

Datasheet

HSS Jobber Drill Bit



Description:

Manufactured to DIN 338 with right hand spiral.

Point angle 118°.

Ideal for general workshop or maintenance use where precision and high productivity are not required.

Black finish for corrosion and wear protection.

Material: HSS M2



RS Stock No.	Diameter(mm)	Overall Length (mm)	Flute Length (mm)
212-991	1.0	34	12
212-985	1.5	40	18
212-979	2.0	49	24
213-089	2.5	57	30
212-963	3.0	61	33
212-957	3.3	65	36
213-073	3.5	70	39
213-067	4.0	75	43
213-051	4.2	75	43
213-023	4.5	80	47
213-045	5.0	86	52
213-039	5.5	93	57
213-095	6.0	93	57
213-168	6.5	101	63
213-146	7.0	109	69
213-130	7.5	109	69
213-124	8.0	117	75
213-118	8.5	117	75
213-102	9.0	125	81
212-929	10.0	133	87
212-913	10.2	133	87
212-907	10.5	133	87
212-884	11.0	142	94
212-878	12.0	151	101
212-935	13.0	151	101