



verso mobile drawer cabinet with 7 drawers & top tray with mat. Featuring a robust, fully welded steel housing with push - pull handle, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 6x 100mm, 1x 125mm (50kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 800x550x965mm

Breite [mm]: 800
Tiefe [mm]: 550
Höhe [mm]: 965
Bruttogewicht [kg]: 89.70
EAN-Code: 5039350116654
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	7
Drawer load capacity [kg]	50
Drawer height 1 [mm]	100
Drawer height 2 [mm]	100
Drawer height 3 [mm]	100

Drawer height 4 [mm]	100
Drawer height 5 [mm]	100
Drawer height 6 [mm]	100
Drawer height 7 [mm]	125

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Top tray and mat
--------------------------	------------------