

Synchronous time switch Week 1 change-over contact 230 V/50 Hz 3 MW



Figure similar

Model	
Product brand name	SENTRON
Product designation	Timers
Design of the product	Week
Design of the switching function	CO contact
General technical data	
Manner of function	
• line-synchronous	Yes
• quartz-controlled	No
Shortest switching time interval / of channel 1	240 min
Supply voltage	
Supply voltage / initial value	230 V
Supply voltage / Full-scale value	230 V
Supply voltage frequency	
• minimum	50 Hz
• maximum	50 Hz

Type of voltage / of the supply voltage	AC
---	----

Protection class

Protection class IP	IP20
---------------------	------

Switching capacity

Switching capacity current / at AC / at 250 V / Rated value	16 A
---	------

Product details

Product feature / floating switching contact	Yes
--	-----

Product function

Product function	
• 60 min time program	No
• Automatic daylight-saving adjustment	No
• direct operation	Yes
• annual time program	No
• Switching preselection	Yes
• 24-hour time program	No
• Weekly time program	Yes

Number

Number of channels	1
--------------------	---

Mechanical Design

Height	83 mm
Width	53 mm
Depth	64 mm
Number of width units	3
Mounting type	DIN rail
Net weight	153 g

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7LF5300-6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7LF5300-6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF5300-6

