



**FMHT13127-0 - STANLEY® FATMAX™
10"/250mm Quick Adjustable Wrench**



STANLEY® FATMAX™ 10"/250mm Adjustable Wrench – FMHT13127-0

- Quick adjusting for fast and accurate settings
- Black phosphate finish for maximum strength and durability
- Parallel jaws placed at a 15° offset angle provide firm grip and best reach
- Thin and wide jaws offer greater accessibility when working in tight spaces
- Bi-material grip for guaranteed comfort of use and ultimate control
- Metric and Imperial scales for maximizing the tightening applications
- Hanging hole for securing the tool to a lanyard

Jaw Style – Thin Jaw

Scale – Metric and Imperial (mm/inch)

Finish – Black Phosphate

Handle Material – Bi-Material

Length – 250mm

Number of Pieces - 1