

CISA C2000 CYLINDERS

- Providing a medium level of physical security these cylinders are an economical option for either singles or master keyed systems.
- Hardened steel pin and driver in first position protects from drilling
- 5 pin key biting system offers over 30000 key differs
- Anti-pick profiled brass pins and drivers
- DIN standard Sintered steel cam provides push resistance to prevent the cylinder being forced out of the lockcase
- 3 keys supplied as standard



OG300.07



TIMBER DOORS STEEL DOORS

Code	Description	Size	Finish
OG300.07	C2000 Euro Profile Double Cylinder	30/30mm	SB / SNP
OG300.13	C2000 Euro Profile Double Cylinder	30/35mm	SB / SNP
OG300.18	C2000 Euro Profile Double Cylinder	40/40mm	SB / SNP
OG302.07	C2000 Euro Profile Cylinder & Turn	30/30mm	SB / SNP
OG302.13	C2000 Euro Profile Double Cylinder	35/35mm	SB / SNP
OG302.18	C2000 Euro Profile Double Cylinder	40/40mm	SB / SNP

LEGGÉ VALUE CYLINDERS

- Euro profile replacement cylinders
- 3 Keys



Code	Description	Size	Finish	Barcode
P801	Single Cylinder - Euro Profile	46mm	PB	5 010564 031209 >
P801	Single Cylinder - Euro Profile	46mm	SCP	5 050640 022561 >
P802	Double Cylinder - Euro Profile	35/35mm	PB	5 010564 031223 >
P802	Double Cylinder - Euro Profile	35/35mm	SCP	5 050640 022578 >
P803	Cylinder & Turn - Euro Profile	35/35mm	PB	5 010564 031247 >
P803	Cylinder & Turn - Euro Profile	35/35mm	SCP	5 050640 022585 >
P805	Double Cylinder - Euro Profile	35/45mm	PB	5 010564 031285 >
P805	Double Cylinder - Euro Profile	35/45mm	SCP	5 050640 022592 >
P806	Cylinder & Turn - Euro Profile	35/45mm	PB	5 010564 031292 >
P806	Cylinder & Turn - Euro Profile	35/45mm	SCP	5 050640 022608 >