


558-00311



Article Number: 558-00311

Solid Colored Continuous Roll, 2.0" X 250', Vinyl, Black 250ft/RL



Base Data

Local Order Number 558-00311

Type HT2BK250

Color Black (BK)

Features and Benefits

- Continuous Vinyl Labels are made with UV stable materials for long outdoor life.
- Labels are extruded in the actual color and not colored using surface inks for long term fade resistance.
- Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

Product Description Continuous Vinyl Labels are made with UV stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long term fade resistance. The Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

Short Description Solid Colored Continuous Roll, 2.0" X250', Vinyl, Black 250ft/RL

Product Dimensions

Length L (imperial) 250.0 ft

Length L (metric) 76.2 m

Width W (imperial) 2.0 "

Width W (metric) 50.8 mm

Height H (imperial) 2.0 "

Height H (metric) 50.8 mm

Print Method Thermal Transfer

Vertical Repeat VR (imperial) 2.0 "

Vertical Repeat VR (metric) 50.8 mm

Width of Liner WL (imperial) 2.0 "

Width of Liner WL (metric) 50.8 mm

Logistics and Packaging

Quantity per roll

Package Quantity (imperial) 250 ft

Package Quantity 76.2 m

Labels per Column 1

Labels per Row 1

Material and Specifications

Material Vinyl

Material Shortcut Vinyl

Adhesive Acrylic

Shortcut Adhesive Acryl

Adhesive Operating Temperature -40 °F to +180 °F (-40 °C to +82 °C)

Operating Temperature -40 °F to +180 °F (-40 °C to +82 °C)

ROHS Conformity Yes