


## Features

- LED backlit panel solutions for a range of commercial applications
- Slim profile, white aluminium frame with high quality TP(a) diffuser, providing low glare (UGR<19)
- Compatible with RS PRO's selectable Self-Test or Manual-Testdual plug-in emergency pack.
- Quick fix connector with loop in, loop out terminals provide for an easier and more economical installation.
- Suitable for suspended ceilings and surface with suspension mounting kits available.
- 5-year guarantee

## RS PRO LED Backlit Panel Lights 600x600 TP(a) with Low Glare URG<19

RS Stock No.: 0555908



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# LED Panel Lights

## Product Description

RS PRO LED backlit panels offer adjustable colour temperatures of 3000K (Warm White), 4000K (Cool White), and 6000K (Daylight), making them ideal for a wide range of commercial applications.

Designed with a sleek white aluminium frame and a high-quality TP(a) diffuser, they provide low glare (UGR<19) for enhanced visual comfort

## General Specifications

Luminosity	4400lm
Light Source Luminosity	5200lm
Efficiency	135lm/W
Operating Current	0.136A
Power Factor	0.98
Colour Temperature	3000K / 4000K / 6000K
Beam Angle	90°
Dimmable	No
Energy Rating	D
Lifespan	50,000 Hours
Warranty	5 Years

## Electrical Specifications

Wattage	32W
Voltage Rating	220-240V

## Mechanical Specifications

Length	595mm
Width	595mm
Depth	30mm

# LED Panel Lights

---

IP Rating	IP20
IK Rating	IK02

## Operation Environment Specifications

---

Operating Temperature	-10~45°C
-----------------------	----------

## Approvals

---

Compliance/Certifications	LVD, EMC, RoHS
Standards Met	BS EN 60598-1