

Specifications

Photo is representative

Eaton 7.2WFNHO31.5

Motor fuse-link, medium voltage, 31.5 A, AC 7.2 kV, 76 x 403 mm, back-up, BS, with striker

General specifications

PRODUCT NAME	Eaton Bussmann series medium voltage motor fuse
CATALOG NUMBER	7.2WFNHO31.5
MODEL CODE	7.2KV 31.5A 3" MOTOR START FUSE
EAN	5027590488686
PRODUCT LENGTH/DEPTH	403 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	4400 g
COMPLIANCES	CE
PRODUCT TYPE	Medium voltage motor fuse



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	31.5 A
INTERRUPT RATING	40 kAIC
RESISTANCE	25.5 ohms
VOLTAGE RATING	7.2 kV
WATT LOSSES	35 W

Physical Details

PACKAGING TYPE	Standard
TYPE	fuse

General Information

APPLICATION	Motor protection
CLASS	Class back-up
CONSTRUCTION SIZE	76 x 403 mm
FUSE TYPE	WFNH
USED WITH	A3354730 Nickel-plated copper fuse clip

Resources

BROCHURES	eaton-bussmann-circuit-protection-brochures-en.pdf
-----------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

