


Insert strip - ES/KMK 3-GB - 1005088

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, Plotter, Mounting type: Insert, Lettering field: 17.2 x 39.75 mm



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 012397
Weight per Piece (excluding packing)	10.68 g
Custom tariff number	48025890
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	297 mm
Width (a)	210 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Print image may vary depending on laser printer
Color	white
Components	free from silicone and halogen
Material	Polyester foil
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	52
Number of individual labels per row	4
Marking mounting type	Insert

Insert strip - ES/KMK 3-GB - 1005088

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410