

MC20

 6 kg

74

	art.	
027500020	MC20	soft thermoformed tray with tool assortment
027510024	MCV24	Tray MC20, empty



- n. 31 **861MIX/A31**: 30 bits with quick release magnetic bit holder, ● ○ ⊕ ⊕ ⊕
- n. 1 **895/1**: socket holder
- n. 1 **1048N**: slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 1 **1370**: engineer's hammer 300 g
- n. 1 **32**: centre punch Ø 4 mm
- n. 1 **36**: cape chisels, standard type Ø 4 mm
- n. 13 **900**: 1/4" hexagon sockets ○ 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
- n. 1 **900/21**: 1/4" drive extension bar 150 mm
- n. 1 **900/25**: 1/4" drive universal joint
- n. 1 **900BG/30C**: 1/4" drive spinner handle
- n. 1 **900/42**: 1/4" drive swivel T-handle
- n. 1 **900/55**: 1/4" reversible ratchet ⊕
- n. 16 **920A**: 1/2" square drive hexagon sockets ○ 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 - 27 - 30 - 32 mm
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920AN/125**: 1/2" wobble extension bar 125 mm
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/55**: 1/2" reversible ratchet ⊕