

Terminal housing f. motor Han 10B 73, co



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 410 0971
Specification	Terminal housing f. motor Han 10B 73, co
HARTING eCatalogue	https://harting.com/09304100971

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Drive®
Type of hood/housing	Housing for motor application
Description of hood/housing	With thermo-plastic cover

Version

Size	10 B
Locking type	Single locking lever
Han-Easy Lock®	Yes

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12
Distance assembly fixing holes	73 mm

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Material (seal)	NBR



Pushing Performance
Since 1945

Material properties

Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	2d63e3a4-7abb-4e67-bb13-55bff2df44a0
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	275.3 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048560
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466