

Dell EMC DAC-SFP-10G-3M Compatible 3m 10G SFP+ to SFP+ Direct Attach Cable Twinax - 10GbE SFP+ Copper DAC 10 Gbps Low Power Passive Mini GBIC/Transceiver Module DAC

Product ID: DACSFP10G3M



The DACSFP10G3M is a Dell EMC DAC-SFP-10G-3M compatible direct-attach copper SFP+ cable that's designed, programmed and tested to work with Dell EMC brand compatible switches and routers and complies with MSA industry standards.

This passive Twinax copper cable supports 10 Gigabit Ethernet applications connected through SFP+ (Mini-GBIC) ports. This copper SFP+ cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

Designed for high-speed performance, this low-power, low-latency 10GbE cable is a cost-effective alternative to fiber-optic cable assemblies, supporting short-distance applications such as point-to-point in-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- 100% DELL EMC DAC-SFP-10G-3M COMPATIBLE DAC: 10G direct attach cable works with Dell EMC switches and is MSA compliant
- TECHNICAL SPECS: 3m (9.8ft) 10 Gbps Passive Twinax (Copper) 2 x SFP+ Pluggable Connector 100 Ohm

Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant

• TECHNICAL SPECS: 3m (9.8ft) 10 Gbps Passive Twinax (Copper) 2 x SFP+ Pluggable Connector 100 Ohm Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant

• TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Dell EMC routers and switches

• LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself, not the life of your switch; our modules won't void your OEM warranty and supported by our Tech Advisors 5/24

• Hot-swappable with fiber-optic modules

Hardware

Warranty	Lifetime
Compatible Brand	Dell EMC
Cable Type	Passive Copper Cable

Performance

Maximum Data Transfer Rate	10.00 Gbps
Impedance	100 Ohm
Type	Copper
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	61,728,395 hours
Power Consumption (In Watts)	< 1W

Connector(s)

Connector A	SFP Slot
Connector B	SFP Slot

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	0~85% RH



Physical Characteristics

Product Length	9.8 ft [3.0 m]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [12 mm]
Weight of Product	5.3 oz [150 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	5.3 oz [150 g]

What's in the Box

Included in Package	SFP+ Cable
---------------------	------------

****Product appearance and specifications are subject to change without notice.***

