



M18 FUEL 100mm Variable Speed Braking Grinder

M18 FSAGV100XPDB-0X0

- Generates Corded Power - Powerful POWERSTATE Brushless Motor spins at 8,500 RPM and allows the user to complete the toughest grinding and cutting applications
- Increased Control - Variable speed control for applications that require lower RPM grinding; 3500 - 8500 RPM
- 5 Speed Settings

MODEL VARIANT



INCLUDES

- M18 FSAGV100XPDB (1)
- FIXTEC Nut (1)
- Dynacase (1)
- Safety Guard (1)
- Side Handle (1)

Categories: Grinders

WHAT'S INCLUDED

M18 FSAGV100XPDB-0X0

M18 FSAGV100XPDB (1)
Safety Guard (1)
FIXTEC Nut (1)
Side Handle (1)
Dynacase (1)

PRODUCT SPECIFICATIONS

Length (mm)	333.3
Height (mm)	111.9
Battery platform	M18 REDLITHIUM-ION
Voltage (V)	18
No Load Speed (rpm)	3,500 -8,500 RPM
Disc diameter (mm)	100
Weight with battery pack if applicable (kg)	2.6 kg (w/5.0Ah battery)