

PG167 & PG163 = Material: Stainless steel, Material no. 1.4301/ UNS S30400

Band width 7 mm, thickness 0.6 mm, Ear width 10 mm

PG126 = Material: Band & Housing Stainless steel, Material no. 1.4016/ UNS S43000, Hex Head screw: steel, zinc plated

Band width 9 mm, thickness 0.6 mm



Part number	Pcs/Bag	Dia. Range
18500220	5pcs/bag	12.0 - 20.0 mm(PG126)
18500221	5pcs/bag	23.6 - 30.0 mm(PG163)
18500222	10pcs/bag	08.8 -10.5 mm(PG167)
18500223	10pcs/bag	09.8 - 12.3 mm(PG167)
18500224	10pcs/bag	11.3 - 13.8 mm(PG167)
18500225	10pcs/bag	12.0 - 14.5 mm(PG167)
18500226	10pcs/bag	13.2 - 15.7 mm(PG167)
18500227	10pcs/bag	17.8 - 21.0 mm(PG167)
18500228	10pcs/bag	16.6 - 19.8 mm(PG167)
18500229	10pcs/bag	19.4 - 22.6 mm(PG167)

