

FEATURES

- Galvanised steel construction
- Easy to inspect for damage
- Shock absorbing
- High resistance to abrasion
- Fatigue rated at 1 – times the working load limit at 20 000 cycles

RS PRO Eye Bolt M16 x 20mm

RS Stock No.: 673-658



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These Eye Bolts from our own RS PRO brand are intended for linear pulling loads in the direction of the thread. These Eye Bolts are proof tested and supplied complete with test certificate.

General Specifications

Type	Eye Bolt
Working Load Limit	0.8t
Material	Carbon Steel

Mechanical Specifications

Diameter	20mm
Thread Size	M16
Thread Length	23mm
Collar Diameter	29mm
Collar Thickness	10mm
Eye Outside Diameter	44mm
Overall Height	71mm
Applications	Tensioning wires, Securing loads

Safety Standard

Standards Met	BS 4278:1984
----------------------	--------------

