

Product information

7.2V Pencil Impact Driver



TD022DSE

Vibration: Impact Fastening	7.0 m/sec ²
Battery Type	Lithium-ion
Battery Ah	1.5 Ah
Voltage	7.2 v
Electric Brake	1
Driving Shank	6.35mm (1/4") Hex
Impacts per minute	0 - 3000 ipm
Machine Screw	M3-M8
Standard Bolt	M3-M8
High Tensile Bolt	M3-M6
Coarse thread (length)	22 - 45 mm
Noise sound pressure	85 dB(A)
Noise sound power	96 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 2450 rpm
Max Torque	25 Nm
Vibration K factor	1.5 m/sec ²
Net weight	0.56 kg



STANDARD EQUIPMENT: 198000-3 7.2V Li-ion Battery , DC10WA 7.2V-10.8V BATTERY CHARGER, Phillips bit, Carry case, Drill holster

- Variable speed
- Forward/reverse rotation
- LED job light
- Electric brake
- Ergonomic soft grip

Details correct as of: 25-5-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com