



brennenstuhl® Connect LED WiFi spotlight with infrared motion detector WFD 3051 P 4300 lm, PIR, IP 54

For outdoor use, IP 54.



Product number 1179060020
EAN 4007123694365

DESCRIPTION

- LED spotlight with super-bright Everlight SMD LEDs.
- Ideal for automatic illumination of entrance areas, driveways or carports as well as for deterring burglary and theft.
- Detection range up to 12 m, with a detection angle of 160°.
- Day/night sensor sensitivity and light duration 5sec to 60min.
- Simple commissioning and control with free brennenstuhl®Connect app.
- Control of various light functions via brennenstuhl®Connect App:
 - Stepless adjustment of light intensity.
 - Stepless adjustment of the light temperature from cold white to warm white.
 - Timer and countdown.
 - Event records.
 - Programmed afterglow.
- Voice control via Amazon Alexa or Google Assistant.
- Spotlight head can be swivelled horizontally and vertically.

TECHNICAL DATA

Luminous efficacy	120 lm/W
Min.-max. colour temperature	3000 K - 6500 K
Colour rendering index	80-89 (class 1B)
Fluorescent colour	white
With motion detector	Yes
Max. detection range	12 m
Min.-max. duty cycle	5 s - 60 min

Power consumption	36 W
Min.-Max. Nominal input voltage	220 V - 240 V
Impact strength	IK06
Protection class	I
Degree of protection (IP)	IP54
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	0.65 kg
Dimension LxWxH (without packing)	23.4 cm x 13.3 cm x 19 cm

Weight of product (including packaging)	0.85 kg
Dimension LxWxH (incl. packing)	13.6 cm x 25 cm x 13 cm

SCOPE OF DELIVERY

brennenstuhl®Connect LED WiFi spotlight WFD 3051 P, mounting material

Hugo Brennenstuhl GmbH & Co. KG

www.brennenstuhl.com

All products are subject to technical changes.