

## Technical Information

Tecno line

### Utility cabinet, Broom Cupboard

Code	<b>M080-000000001</b>
Name	Welded all-purpose cabinet
Dimensions (WxDxH)	800x400x1800 mm
Comp. Dim. (WxDxH)	798x380x1700 mm
N° places	1
N° comp. per column	1
Material	DC01/FeP01 UNI EN 10130
Weight (Kg)	37
Volume (m3)	0,58



### General features

Base and body	Base on steel socle h. 100 mm. Body formed by electro-welded paneling 6/10 thick, Bottom, top, back, sides with racks front thickness 30 mm and refolded edges.
Doors	Hinged doors with external 180° rotation angle°, reinforcement and three-times anti-cut bending.
Lock	Cylinder lock with 2 keys
Closing	Two points closing lever
Internal construction	4 movable shelves on rack, with galvanized steel shelf supports
Door color	Painting with epoxy powder color RAL 7035.
Body color	Painting with epoxy powder color RAL 7035.
Law	In specification D.Lgs.81/2008, EN UNI ISO 9001, EN UNI ISO 14001, UNI tests on product and finishing.

### Configuration variants

Base	Stainless steel Inox
Doors	Door free
Locks	Padlock
Closing	Three way
Internal construction	Broom holder with separation and 4 side shelves

Door color	 6018 3003 5012 5015 5010 7035	Body color	 7035
------------	--	------------	--

### Accessories

Shelf, complete with galvanized steel schelf supports.

### Spare parts

Cylinder lock supplied with double key  
Left or right hinged door H. mm. 1670

### Certifications

Check the list of certifications available in the appropriate section of the website or ask our commercial offices.

This technical sheet is exclusive property of Armet Srl.

Reproduction is forbidden within the law (art.171 Law 22/04/1941 ,n.633).

The fraudulent use, without proper written authorization, even partial and by whatever means, will be protected according to law.

The foregoing text contains information reserved to the intended recipient.

The content of this e-mail is confidential and its confidentiality is legally protected by DL196/03