

Long-cuffed neoprene chemical-resistant gloves, offering advanced mechanical and chemical protection

- **Advanced protection:** AlphaTec® 09-430 industrial gloves' high-grade neoprene compound and smooth finish can withstand various mechanical and chemical hazards, including acids, oils, caustics, alcohols, and solvents
- **Elevated comfort:** These heavy-duty chemical-resistant gloves also feature a cotton jersey liner, which enhances wearer comfort while boosting protection against snags and punctures
- **Refined ergonomics:** AlphaTec® 09-430 hand protection gloves' anatomical design is shaped to the contours of the hand at rest, resulting in greater dexterity and lesser hand fatigue over time
- **Enhanced features:** These AlphaTec® gloves measure 800mm/31", ensuring more comprehensive personal protection that reaches the wearer's shoulder



Industries

- Metal fabrication
- Chemical

Applications

- Foundry operations
- Handling materials with sharp or rough edges
- Extruding, bending and punching shapes
- Processing sheets, coils, tubes
- Fabricating metal parts, glass sheets
- Unexpected leakages spills or other releases

Previously known as: Scorpio™ 09-430

Key Features

- **High-grade neoprene with smooth finish:** Advanced chemical resistance
- **Cotton jersey liner:** For truly comfortable, abrasion-resistant gloves
- **Anatomical design:** Greater dexterity, lesser hand fatigue

Vulcanization Chemical Accelerators

- Diphenyl guanidine
- Diphenyl thiuram urea

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 09-430	Liner Material: Cotton Jersey Coating Material: Neoprene	10	800 / 31.5	Black	• 1 pair per bag, 12 pairs per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.