



Main

Range of product	Mita
Product or component type	Mini trunking
Colour tint	White
Quantity per set	90 m

Complementary

Compartment partitioning	1 compartment
Trunking dimension	16 x 16 mm
Fixing mode	Adhesive
Material	UPVC (unplasticized polyvinyl chloride)
Length	3000 Mm
Height	16 Mm
Width	16 Mm




Environment

Standards	BS 4678-4
Ambient air temperature for operation	-5...60 °C

Packing Units

Package 1 Weight	1.000 G
Package 1 Height	1.000 Mm
Package 1 width	1.000 Mm
Package 1 Length	1.000 Mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

China RoHS Regulation

[China RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Contractual warranty

Warranty

18 months

Product Life Status :	Commercialised
-----------------------	-----------------------