

## Features

- Corrosion-resistant screws
- Easy wiring installation
- Thermoplastic body
- Zinc-plated steel terminal screws

## RS PRO Term Strip Barrier 10Poles 30A 600V Thermoplastic

RS Stock No.: 0458770



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

From RS PRO, this non-fused terminal block presents a reliable and cost-effective solution to wire to-wire connections. This lightweight and robust terminal block is designed for free hanging or panel mount applications.

## General Specifications

Fused	NO
Mounting Type	Free Hanging, Panel Mount
Contact Material	BRASS
Termination Method	SCREW
Material	Thermoplastic
Number of Ways	10
SCREWS	zinc-plated steel

## Mechanical Specifications

Optional cable size	22~10AWG
Suggested screw torque	12Ib.-in.
Operating Temperature	125°C maximum

## Electrical Specifications

Voltage Rating	600VAC RMS maximum
Current Rating	30A Amps maximum

## Approvals

Standards Met	UL Recognized
Declarations	CE/UKCA Declaration of Conformity

## DIMENSION

