

3024 0,6
Folding hydraulic crane with dual effect pump
CE

An ideal solution for small working spaces or loads.


With its slender yet sturdy frame, foldable levers and a pumping unit that can be rotated 200°, it ensures both convenience and comfort, even in smaller spaces.

The loading arm can be adjusted in 5 positions, reaching a maximum height of 2300 mm and a working radius ranging from 960 mm to 1350 mm.

 73 Kg

Features:

- Maximum carrying capacity: 600 kg
- 5 loading positions: 400-450-500-550-600 kg
- With load limiting valve and chrome-plated stand
- Controlled descent speed
- Nylon wheels
- Maximum height: 2300 mm
- Working radius of arm: min. 960 mm – max. 1350 mm
- Operating unit can be rotated 200°

	art.	H	H1	P	P1	L
030240006	3024 0,6	1540	2300	925	390	1375

