

VARTA Recharge Accu Power AA 2600 mAh Blister 4



The most powerful product line with durable and precise energy supply for all standard and smart applications of daily use.



Information

- Pre-charged and with 'ready to use' technology - for immediate usage straight from the pack
- Highest 'ready to use' capacity for AA NiMH batteries with 2600mAh
- Suitable for the most demanding standard and smart devices of daily use and all NiMH chargers
- Best use in high drain applications like game controllers, toys, photoflashes and more devices
- Lasts up to 10 times longer in digital cameras*
- * vs. VARTA Energy. Based on IEC 60086-2 (ed. 14.0) HDA-Test (high drain application). May vary by device.

Article Details

Ordernumber	05716 101 404
Customs Tariff Number	85075000
Country Of Origin	China
IEC	HR6
Others	5716, AA, Stilo
Nominal Capacity	2600 mAh
Voltage	1.20
System	Nickel Hydride
Consumer Unit	4
DG Profile	NiMH battery UN3496 (sea to 100kg ok)

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 745975	80.00	16.00	120.00	0.13
SK2 (Inner carton 2)						
SK1 (Inner carton 1)	10	40 08496 745982	89.00	126.00	83.00	1.36
VSK (Master carton)	100	40 08496 745999	135.00	425.00	183.00	13.69
PAL (Pallet)	7800	40 08496 746002	800.00	1,200.00	1,248.00	1,088.66
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
6	13		78		10	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

