

## Pear Head Ratchets

3 Pear Head Ratchets

### Sealed and Robust

#### Ultra-Resistant and Sealed Head for Longer Life

- Double sealing gasket: mechanism sealed and dust free.
- Maintenance free.
- Tested in aggressive conditions.



#### High Precision

- SCMT14970  
1/2Dr 72 teeth for 5" increments dimensions 120mmL x 20mmW
- SCMT13970  
3/8DR 72 teeth for 5" increments dimensions 210mmL x 25mmW
- SCMT12970  
1/4DR 52 teeth for 7" increments dimensions 260mmL x 38mmW

#### Reduced Fatigue:

- Lighter ratchets (Than traditional lever ratchets.)
- Center of gravity moved towards the head for easier increment movements.

#### Palm Control System

- For more powerful loosening.



#### Recessed Reverse Lever

- Avoids accidental reversal and is easier to operate with gloved hands.



#### Comfortable:

- No discontinuity between the plastic and metal sections.

#### Hook Eye



## Metric Inhex Sockets

Part No.	Barcode	Size
SCMT14280	9311927142805	6 x 60mm
SCMT14281	9311927142812	7 x 60mm
SCMT14282	9311927142829	8 x 60mm
SCMT14283	9311927142836	10 x 60mm
SCMT14284	9311927142843	12 x 60mm
SCMT14285	9311927142850	14 x 60mm
SCMT14286	9311927142867	17 x 60mm
SCMT14287	9311927142874	8 x 135mm
SCMT14288	9311927142881	10 x 135mm



## AF Inhex Sockets

Part No.	Barcode	Size
SCMT14470	9311927144700	3/16" x 60mm
SCMT14471	9311927144717	7/32" x 60mm
SCMT14472	9311927144724	1/4" x 60mm
SCMT14473	9311927144731	9/32" x 60mm
SCMT14474	9311927144748	5/16" x 60mm
SCMT14475	9311927144755	3/8" x 60mm
SCMT14476	9311927144762	1/2" x 60mm
SCMT14477	9311927144779	9/16" x 60mm
SCMT14478	9311927144786	5/8" x 60mm



## Spline Type Inhex Sockets

Part No.	Barcode	Size
SCMT14295	9311927142959	M6 x 60mm
SCMT14296	9311927142966	M8 x 110mm
SCMT14297	9311927142973	M10 x 110mm
SCMT14298	9311927142980	M12 x 110mm



## 12 Point Spark Plugs

Part No.	Barcode	Size
SCMT14445	9311927144458	5/8"
SCMT14446	9311927144465	13/16"



SCMT14904

## BigFella Ratchet

Barcode: 9311927149040

- 36 Tooth mechanism for a 10° arc swing
- Quick-Release
- Male
- 425mm



SCMT14906

## Reversible Ratchet

Barcode: 9311927149064

- 36 Tooth mechanism for a 10° arc swing
- Quick-Release
- Male
- 250mm



SCMT14907

## Swivel Head Ratchet with T-Bar Handle

Barcode: 9311927149071

- 60 Tooth gear for a small 6° arc swing
- 180° Swivel head
- T Bar handle
- Male
- 340mm



SCMT14919

## Microtough Ratchet

Barcode: 9311927149194

- Smallest ratchet head in the industry providing access to confined areas
- 72 Tooth gear for a small 5° arc swing
- Reversible
- Male
- 250mm



SCMT14970

## 1/2" Drive Maintenance Free Pear Head Ratchet

Barcode: 9311927149705

- Fully Sealed Head
- Ergonomic Handle
- Maintenance Free
- Length: 262mm
- 72 teeth



SCMT13970

## 3/8" Drive Maintenance Free Pear Head Ratchet

Barcode: 9311927139706

- Fully Sealed Head
- Ergonomic Handle
- Maintenance Free
- Length: 210mm
- 72 teeth



## Extensions - Male & Female

- Male & Female

Part No.	Barcode	Size
SCMT13915	9311927139157	75mm
SCMT13916	9311927139164	150mm
SCMT13917	9311927139171	250mm
SCMT13918	9311927139188	500mm



## Extensions - Male & Female Wobble

- Male & Female
- Allows sockets to be driven at up to 15° angle

Part No.	Barcode	Size
SCMT13920	9311927139201	75mm
SCMT13921	9311927139218	150mm
SCMT13922	9311927139225	250mm



SCMT13925

## Adjustable Offset Handle

Barcode: 9311927139256

- 220mm



SCMT13928

## Sliding T Handle

Barcode: 9311927139287

- 200mm



SCMT13930

## Speed Brace

Barcode: 9311927139300

- 400mm



SCMT13950

## Universal Joint

Barcode: 9311927139508

- Link Joint



SCMT70274

## 3/8" Socket Holding Rail

Barcode: 9311911702749

- Neatly stores sockets in toolbox or on workbench
- Clearly shows missing sockets



SCMT19155

## Adaptor

Barcode: 9311927191551

- 3/8" Female to 1/4" Male



SCMT19157

## Adaptor

Barcode: 9311927191575

- 3/8" Female to 1/2" Male



SCMT12909

## Universal Joint

Barcode: 9311927129097

- Link Joint



SCMT12910

## Socket Driver

Barcode: 9311927129103

- 150mm



SCMT12914

## Rotator Ratchet

Barcode: 9311927129141

- Twist action handle for tight spaces
- Rotates with 0° swing
- 60 Tooth gear for a small 6° arc swing
- Dual Function
- Male
- 185mm

### Rotator™



Continuous drive using twist action handle

SCMT12919

## Microtough Ratchet

Barcode: 9311927129196

- Smallest ratchet head in the industry providing access to confined areas
- 72 Tooth gear for a small 5° arc swing
- Reversible
- Male
- 140mm



SCMT12970

## 1/4" Drive Maintenance Free Pear Head Ratchet

Barcode: 9311927129707

- Fully Sealed Head
- Ergonomic Handle
- Maintenance Free
- 52 teeth



Replaces SCMT12905

**PROTO**

J4749

## 1/4" Drive Ratchet

Barcode: 662679141288

- 24 Tooth mechanism for a 15° arc swing
- Reversible
- Male
- 127mm



SCMT70272

## 1/4" Socket Holding Rail

Barcode: 9311911702725

- Neatly stores sockets in toolbox or on workbench
- Clearly shows missing sockets

