



Main

Range of product	Acti 9 Librio Prodis Clario
Product or component type	Shunt trip release with OC contact
Device short name	MX + OF
Signal contacts composition	1 C/O
[Uc] control circuit voltage	48 V AC 50/60 Hz 48 V DC
9 mm pitches	2

Complementary

Range compatibility	Acti 9 iDPN Acti 9 C120 Acti 9 C40 Acti 9 C60H-DC Acti 9 C60NA-DC Acti 9 C60PV-DC Acti 9 DPN Vigi Acti 9 DT40 Acti 9 DT60 Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40 Acti 9 ID Acti 9 DPN
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	65 g
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 2.5 mm ² - flexible
Wire stripping length	9 mm
Tightening torque	1 N.m
Compatibility code	MX + OF

Environment

Standards	EN/IEC 60947-5-1
Product certifications	LCIE ASEFA KEMA ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Package 1 Weight	77 g
Package 2 Weight	674 g
Package 3 Weight	6.538 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------