

27102 BLOW GUNS FITTED WITH ADAPTOR

Blow gun with metal nozzle

Profile : ISO 6150B



Part number	Max. operating pressure (bar)	Flow rate (l/min)	ID passage (mm)	Level sound (DBA)	Net weight (Kg)
27102 MT6I	10.00	380.00	6 mm	83.00	0,01933

Part number
27102 MT6I