



Main

| | |
|-------------------|----------------------------------|
| Range of product | Opale Pragma D |
| Device short name | Distri'clicXE distribution block |

Complementary

| | |
|-------------------------------|-------------------------------------|
| [In] rated current | 63 A (40 °C) |
| [Ui] rated insulation voltage | 250 V AC |
| 9 mm pitches | 10 |
| Connections - terminals | Cable connectors 16 mm ² |

Environment

| | |
|--------------------------|-----------|
| RoHS EUR conformity date | 0643 |
| RoHS EUR status | Compliant |