



Housing units TCJT40-XL-N (Series TCJT)

two-bolt flanged housing units, cast iron, eccentric locking collar, T seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
H	172 mm
U	59,1 mm
A	34,5 mm
A ₁	13 mm
A ₂	24 mm
B ₁	56,5 mm
d _{3 max}	58 mm
J	143,5 mm
L	105 mm
N	14 mm
Q	M6
V	105 mm

m	1,7 kg	Mass
C _r	34500 N	Basic dynamic load rating, radial
C _{0r}	19800 N	Basic static load rating, radial
	CJT08	Designation of housing
	GE40-XL-KTT-B	Designation of bearing
	KASK08	Bearing end cap, closed design. To be ordered separately.
		Slot for bearing end cap



