
PRODUCT-DETAILS

316BS4W

316BS4W Wall mounted inlet



General Information

Extended Product Type	316BS4W
Product ID	2CMA167056R1000
EAN	7392696670562
Catalog Description	316BS4W Wall mounted inlet
Long Description	Surface Inlet, earthing sleeve position 4h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Yellow

Ordering

E-Number (Sweden)	2417219
E-Number (Finland)	2420196
E-Number (Norway)	2417219
EAN	7392696670562
Country of Origin	Czech Republic (CZ)
Minimum Order Quantity	1 piece

Dimensions

Product Net Width	99 mm
Product Net Height	132 mm

Product Net Weight	0.41 kg
Mechanical Drawings	9AKK107680A0031

Container Information

Package Level 1 Width	152 mm
Package Level 1 Depth / Length	120 mm
Package Level 1 Height	265 mm
Package Level 1 Gross Weight	0.41 kg
Package Level 1 EAN	7392696670562
Package Level 1 Units	box 1 piece
Package Level 2 Width	800 mm
Package Level 2 Depth / Length	1200 mm
Package Level 2 Height	900 mm
Package Level 2 Gross Weight	71.25 kg
Package Level 2 EAN	7392696070980
Package Level 2 Units	pallet (lift) 125 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

CB Certificate	2CHC660161X0201
Declaration of Conformity - CE	2CMC700005D0001
Environmental Information	2CMC000056M0000
RoHS Information	2CMC700005D0001
SEMKO Certificate	2CHC660161X0201
REACH Declaration	2CMC700005D0001

Additional Information

Additional Information	3P+E
Ambient Temperature	-25 ... 40 °C
Cable Cross-Section	1.5 ... 4 mm ²
Cable Diameter	28.3 mm
Cable Entry Position	Cable entry Ø25mm
Color	Yellow
Connection Type	Screw
Degree of Protection	IP67 IP69
Design	Surface mounted plug

Frequency (f)	50 Hz 60 Hz
Function	Surface inlet
Housing Material	Thermoplastic (PBT)
Invoice Description	Ind. P&S#316BS4W
Mounting Holes	60x148,2
Number of Poles	4
Order Multiple	1 piece
Product Main Type	TBS
Product Name	Wall mounted inlet
Protection Type	Watertight
Rated Current (I_n)	16 A
Rated Frequency (f)	50 ... 60 Hz
Rated Voltage (U_r)	100 ... 130 V
Recommended Screw Driver	PH2
Standards	IEC 60309-1, -2
Suitable For	Surface Inlets
Suitable for Product Class	IEC Industrial Plugs and Sockets
Instructions and Manuals	2CMC700014C0016
RAL Number	RAL 7012 - Basalt Grey

Classifications

eClass	27440519
UNSPSC	39120000

Technical

Wire Size	14 ... 12 AWG
Tightening Torque	WireClamp0.8 N·m

Categories

Low Voltage Products and Systems → Industrial Plugs and Sockets → Tough & Safe → Surface Inlets

