

Steel Rebar Cutter LXT®

DSC191

18V • 3 – 20 mm

Easy cutting of 19 mm steel rods

A powerful cutter for steel rebars. Ideal for cutting steel rods of 8 – 16 mm, with a maximum capacity of 19 mm. Head rotation and quick action without the risk of sparks or kickback.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Cutting time	6,5 s
Cutting Capacity Mild Steel (up to 400N/mm ²)	20 mm
Cutting Capacity Stainless Steel (up to 600N/mm ²)	20 mm
Plastic Carrying Case	✓
Sound Power Level (L _{WA})	90,1 dB(A)
Sound Pressure Level (L _{pA})	80,5 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product Dimensions (L x W x H):	412 x 212 x 284 mm
Tool weight with battery	11,1 -11,2 kg

User benefits

- No dust, no sparks.
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing