

## har-SAB M8/4/3p PAC 10m PUR w/o LED



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 001 0010 000
Specification	har-SAB M8/4/3p PAC 10m PUR w/o LED
HARTING eCatalogue	<a href="https://harting.com/09070010010000">https://harting.com/09070010010000</a>

### Identification

Series	Circular connectors M8
Element	Distribution boxes
Specification	Pre-assembled master cable

### Version

Cable length	10 m
Total number of ports	4
Number of contacts	3

### Technical characteristics

Rated current	6 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

### Material properties

Material (cable)	PUR (polyurethane)
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140276581
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501