

Coaxial Cable Connector 11_MMCX-50-1-1/111_O

Description

Straight cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer 2contact crimped
Weight 0.0009 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--------------------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Brass | Gold Plating (without Nickel underplating) |
| Body | Brass | Gold Plating (without Nickel underplating) |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Brass | |

Related Documents

Outline drawing DOU-00006970
Catalogue drawing DOU-00006168
Assembly instruction DOC-0000179110

Ordering Information

Bulk 100 pcs package 11_MMCX-50-1-1/111_OH
Single package 11_MMCX-50-1-1/111_OE

Additional Information

Suitable cables RG_178_B/U, RG_196_A/U, RG_196_A/U