



Main

Range of product	Cable ends
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Quantity per set	10 sets of 100
Cable cross section	4 mm ²

Complementary

Cable end type	Single conductor
Additional information	For additional marker tag holder
Colour	Orange
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	12
Bezel size	Ø 5.5 mm
Tube diameter	3.3 mm
Length	19.5 mm
Tube length	11.5 mm
CAD overall width	6 mm
CAD overall height	8 mm
CAD overall depth	20 mm
Product weight	0.3 kg

Environment

Product certifications	UL
Ambient air temperature for operation	-20...105 °C