



ENGLISH

Datasheet

Stock No: 680-117

# RS Pro Tool Steel Rectangular Bar, 18in x 6in x 1/2in



## Product Details

### Ground Flat Stock - Metric & Imperial

High quality tool steel fully annealed and free from carburisation

Precision ground to close tolerances, enables finished components to be produced with minimum machining

Suitable for hardening with excellent dimensional stability and resistance to wear

Conforms to BS4659: 1971 BO1

Applications include gauges, punches, dies, jigs, templates, cams, machine parts etc.

Tolerance Imperial; W -0.000 +0.005in; T -0.001 +0.001in

Tolerance Metric; W -0.000 +0.127mm; T -0.000 +0.050 mm

### Ground Stock

## Specifications

Material	Tool Steel
Form	Rectangular Bar
Length	18in
Width	6in
Thickness	1/2in