



PCT-0400-080-YW-50

E1518043

Cable Tie, 368x7.6mm, Yellow Plastic Barb



Product Properties:

Detectable	No
Min. tensile strength	540 N
Model	Internal toothing
Material quality	Polyamide (PA)
Operating temperature	-40-85 °C
Band closure	Plastic lip/-cam
UV-stable acc. ASTM D6779	No
Transparent	No
Fluorescent	No
Solvable fastener	No
Text strip	None
Type of fastening	None
Colour	Yellow
Surface protection	Untreated
Material	Plastic
Halogen free	Yes
Max. tensile force	540 N
Inflammability class of insulation material according to with UL94	V2

Dimensions:

Bundle diameter	3-101 mm
MOQ	50 .

Unit	pcs
Length belt/tape/tie	368 mm
Band width	7.6 mm
Max. tensile force	540 N

Approvals:

Approved according to UR	Yes
UL approval	Yes
Approved according to CE	Yes
Inflammability class of insulation material according to with UL94	V2

Compliance:

CA Proposition 65	In compliance
Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
PFAS	No PFAS
PFOA	No PFOA
PFOS	No PFOS
POPs	No POPs
REACH	No SVHC (247 Subs. 21 Jan 2025)
REACH Annex XIV	No REACH Annex XIV
REACH Annex XVII	No REACH Annex XVII
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000046 - Cable tie
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Cable ties, PCT & CT
Alternative SKU	PCT-0400-080-YW-50
E-no	E1518043

Logistic information:

Barcode	733117640103
Country of origin	CN
E-no	E1518043
Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	50 .

Stock code	PCT-0400-080-YW-50
Taric code	39269097
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.