

Power module - EMD-SL-PS-120AC - 2885731

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Power modules, pluggable, for EMD-SL-..., supply voltage: 108 V AC ... 132 V AC



Why buy this product

- Variable supply voltage range
- Adjustable via potentiometer on the front
- Separately adjustable startup and response delays

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 097055
Weight per Piece (excluding packing)	48.6 g
Custom tariff number	85043180
Country of origin	Germany

Technical data

Dimensions

Width	32 mm
Height	35 mm
Depth	16 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Input data

Nominal input voltage	120 V AC (50/60 Hz)
-----------------------	---------------------

Classifications

eCl@ss

eCl@ss 4.0	27371105
eCl@ss 4.1	27371105

Power module - EMD-SL-PS-120AC - 2885731

Classifications

eCl@ss

eCl@ss 5.0	27049090
eCl@ss 5.1	27049201
eCl@ss 6.0	27049201
eCl@ss 7.0	27049201
eCl@ss 8.0	27049201

ETIM

ETIM 2.0	EC001438
ETIM 3.0	EC001438
ETIM 4.0	EC001438
ETIM 5.0	EC002540

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121535