

Product specifications **380VP**

Last update: 10/30/09 4:41:13 PM

General

Description	Dunlop Pricemastor
Upper/Sole Color	Green/Black
Status	Stock,
Segment	N/A
Product line	Volume
Sizerange/#	35-47/13
Hangtag	
Insole	
Lining	White polyester
Resistance code	1



380VP

Safety

Standard	CE
	<input type="checkbox"/> Steel Toecap <input type="checkbox"/> Antistatic <input type="checkbox"/> Steel Midsole <input type="checkbox"/> Energy absorbing <input type="checkbox"/> Oilresistant sole <input type="checkbox"/> Cold insulating
Safety marking	
Manual	EN manual printed on polybag

Sole info

Sizing	<input checked="" type="checkbox"/> French <input checked="" type="checkbox"/> English <input type="checkbox"/> U.S.
Date of manufacturing	<input checked="" type="checkbox"/>
Other sole info	CE Plan.Plast. Made in P. Pict. R.boot

Labeling/marketing

Marking	Dunlop stamp
Barcode on boot	Barcode label
Barcode packaging	Dunlop label
Barcode outercarton	Dunlop label

Remark

Weight 42: 2,10 kg/pr

Packaging		Sealed milky polybag						
Size	Boxtype	Length	Width	Height	Pairs/Box	Boxes/layer	#Layers	Pallet height
38-43	PT3	390	390	395	8	6	4	1.75
47	PT5	390	390	585	8	6	3	1.92
35-37	PT2	390	390	360	8	6	5	1.95
44-46	PT4	390	390	430	8	6	4	1.8