

### Main

Range	Resi9
Product or component type	Enclosure cover
Nb of 18 mm modules per row	13
Nb of horizontal rows	3
Mounting plate description	Without mounting plate
Width	External: 340 mm
Height	External: 540 mm
Depth	External : 140 mm
Colour	White (RAL 9003)





### Complementary

Enclosure mounting	Flush
Enclosure material	Sheet metal
Net weight	4 kg

### Environment

Standards	NF C 15-100
IK degree of protection	IK07 conforming to EN 50102

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.