




Image may differ from product. See technical specification for details.



TLGB 1262-E

SKF Lincoln Battery Driven Grease Gun TLGB 1262-E

This 12-volt durable battery driven grease gun was developed to simplify and speed up the lubrication process, making it easier for operators to properly maintain equipment. Featuring an updated powertrain, handle design and enhanced features, this grease gun is suitable for agricultural, automotive, construction, some general maintenance and industrial applications.

- Designed for harsh conditions and intensive use
- Cordless lubrication for operator convenience
- Provides effortless, uniform lubricant delivery
- Narrower tool fits in tight areas
- Engineered for long service life
- Ergonomic design is balanced, lighter weight (2.5 kg) and comfortable to grip
- High delivery pressure, up to 550 bars (8000 psi)
- Lithium-ion battery for maximum power and efficiency

Overview

Dimensions

Case dimensions (l x h x w)	590 x 110 x 370 mm
Hose length	760 mm

Performance

Battery capacity	1 500 A·h
Grease output at 70 bar (1000 psi) - Low speed	95 ml/min
Maximum pressure	240 bar

Properties

Battery	12V Li-ion battery
Battery charge time (max)	60 min
Battery charger	200-240V, 50-60 Hz
Built-in light	Yes
Cartridges per battery charge	7
Content	1x Grease gun 1x battery 1x charger 1x instructions for use 1x carrying case
Display	No
Integrated grease metre	No
Maximum peak pressure	550 bar
NLGI class of lubricant (max)	2
Number of available pump speeds	1
Operating temperature range	-15.0 – 50.0 °C

Logistics

Product net weight	5.48 kg
UNSPSC code	15121902
eClass code	23-06-91-06

Compatible products

Spare part

High pressure hose 762 mm (30 in) for SKF TLGB series battery driven grease guns	TLGB 1230
12V Li-Ion battery for SKF battery driven grease gun, TLGB 1262-E	TLGB 1261
Grease tube assembly for battery driven grease gun	TLGB 20-4
Charger 220-240V for battery driven grease gun	TLGB 20-5

Accessory

DC Charger 12-24/12-20V for SKF grease guns, TLGB 1262-E and TLGB 1886-E (Li-Ion)	TLGB 1875A
Carrying strap for battery driven grease gun	TLGB 20-1
High pressure hose 900 mm (36 in) with coupler for battery driven grease gun	TLGB 20-3
SKF Grease Meter LAGM 1000E	LAGM 1000E

Recommended product

SKF Grease Filler Pump LAGF 18	LAGF 18
SKF Grease Filler Pump LAGF 50	LAGF 50
Battery driven grease gun (incl 230V charger)	TLGB 21/230V
Battery driven grease gun (incl 120V charger)	TLGB 21/110V
SKF Lincoln Battery Driven Grease Gun TLGB 1886-E	TLGB 1886-E
High viscosity bearing grease with solid lubricants	LGEM 2/0.4
High load, extreme pressure bearing grease	LGEP 2/0.4
Extremely high viscosity bearing grease with solid lubricants	LGEV 2/0.4
General purpose food grade grease	LGFG 2/0.4
High load, water resistant and wide temperature food grade grease	LGFQ 2/0.4
Biodegradable bearing grease	LGGB 2/0.4
High load, high temperature, high viscosity bearing grease	LGHB 2/0.4

High load, water resistant, high temperature bearing grease	LGHC 2/0.4
High performance, high temperature bearing grease	LGHP 2/0.4
Electric motor bearing grease	LGHQ 2/0.4
High viscosity lubrication systems grease	LGLS 2/0.4
Low temperature, extremely high speed bearing grease	LGLT 2/0.4
General purpose industrial and automotive bearing grease	LGMT 2/0.4
General purpose industrial and automotive bearing grease	LGMT 3/0.4
General purpose, high load industrial bearing grease	LGNL 2/0.4
Wide temperature range, extreme pressure, high load bearing grease	LGWA 2/0.4
Extreme pressure low temperature bearing grease	LGWM 1/0.4
High loads, wide temperature bearing grease	LGWM 2/0.4

Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.