

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5055670471](#)
Status: **Active**
Overview: Micro-Lock Plus Wire-to-Board Connector System
Description: Micro-Lock™ PLUS Right Angle Header, 1.25mm Pitch, Single Row, Tin-Bismuth Plating, 4 Circuits, Black

Documents:

3D Model	Packaging Specification 5055679200-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 5055650000-000 (PDF)	Product Literature (PDF)
Application Specification AS-505565-002-001 (PDF)	

Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	505567
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Literature Order No	987651-4888
Product Name	Micro-Lock PLUS
UPC	889056534239

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	161.548/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact 1.5A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[505567](#) Series

Mates With

Micro-Lock™ PLUS Receptacle Housing
[505565](#)

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

AS-505565-002-001

Packaging Specification

5055679200-200

Product Specification

5055650000-000

Sales Drawing

SD-505567-001, SD-505567-002

This document was generated on 11/01/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION