



NCX I0560

E1665193

CRIMP TOOL INSULATED TERMINALS 0.5-6mm2, SYMMETRICAL

Product Properties:

Number of crimps	1
With locking device (for mechanical tools)	Yes
Inserts exchangeable	Yes
Number of included inserts	1 .
With automatic return	Yes
Cycle time	2 s
Suitable for	Cable lugs and connectors
Construction/operation	Mechanical
For component	Insulated terminals
Compression shape	Oval pressing

Dimensions:

Cross section	0.5-6 mm²
MOQ	1 .
Unit	pcs
Length	235 mm

Approvals:

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Extended Minerals	N/A, contains no extended minerals
REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)

SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000168 - Crimp tool cable lugs, cable end sleeves, screen connection
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	One Hand (ratchet)
Search Description	PRESSVERKTYG ISOLERADE KABELSKOR
Alternative SKU	NCXI0560
E-no	E1665193

Logistic information:

Barcode	733117630548
Country of origin	TW
E-no	E1665193
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	NCX I0560
Taric code	82032000
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.