

# brennenstuhl®

\_ smart technology.

## Brennenstuhl Garant IP44 Cable Reel, 40 metres



**Art. No: 1633120**

**Technical data**

Measures(H/W/D): 44.00/32.50/22.00 cm  
weight g/n 10.147/10. Kg

**Garant IP44 cable reel for site & professional 40m H07RNF 3G2,5**

**Features:**

Reel body made from special plastic fitting to a galvanised steel tube frame.

Innovative and ergonomic cable guide handle "cable pilot" for perfect cable management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.

Rotary handle for comfortable rolling up.

RN cable is approved to exacting site standards as per VDE 0100 part 704.

3 waterjet protected earthed socket outlets with self closing protective caps.

Thermal cut-out protection, indicator shows overheating or overloading.

Design protected.

Cable length: 40 m.

Cable: H07RNF 3G2,5.

Cable quality: Rubber Neoprene.

Cable colour: Black.

Reel Ø:320 mm.