

## **Datasheet**

Product Name: UL3239 22AWG
Product Discription: UL3239 22AWG
Specification No.: SPEC-UL3239-22AWG
Customer's Name:

Description						Construction					
Rated V			6KVDC		Conducto	Conductor Stranded Tinned C					
<b>!</b>	emperature:		105℃		Size(AWG)		22				
Referen	ce Standard:	UL7	58,UL1581		Construction(±0.008mm)		17/0.16				
Cross Section					Stranded Dia.(mm)Ref.		0.76				
					Insulation	n Material	XLPE				
					Insulation	n Color	ANY COLOR				
					Ave Thick	kness(mm)	0.41				
					Min Thick	(ness(mm)	0.36				
					Insulation Dia.(±0.08mm)		1.58				
Marking					Remark:						
					8738970 Brown		8738980 Gr		8738992 Orange	8739009 Violet	
E254881¶ AWM STYLE 3239 22AWG 105℃ 6KV-DC VW						8738974 Red	8738983 Blu		8738996 Grey		
CN AWM I A 105°C 6KV-DC FT1 -LF- ELETECK					8738977 Black 8738986 W			8738999 Yellow			
					Characterist					Customer Approve	
Applications						Test Item			ard Value		
For internal wiring of electronic and electrical equipment						Test Material			E(RoHS)		
					Before	Tensile Strength(Mpa)		≥10.3			
						Aging Elongation(%)			≥150	Seal & Stamp	
						Aging Condiction			℃*168hrs		
Revisions						After Tensile Strength(Mpa)		≥70% of original			
Version	Description		Approved by	Date	Aging	Elongation(%)		≥45% of original			
0	New document issue	YanBin	David Lin	14/04/2015		esistance(20°C Ω/km)			59.4	4	
					Flammability Test			\	/W-1		
										Signature:	
										Dete	
										Date:	

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.