

## 31 KR 25-46

### Friction ratchet handle with insert ring

Bi-hexagon UD profile or bi-hexagon

Code	ETIM
<b>6256550</b>	<b>EC011810</b>
EAN	UNSPSC
<b>4010886625651</b>	<b>27-11-17-11</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-08</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Friction spanner (31 K) with exchangeable UD profile or bi-hexagon insert rings (31 R)
- Hexagonal rings available on request
- Especially suitable for steel and scaffolding construction
- Up to 30" flat shaft, from 35" with slip-on tube
- Vanadium steel 31CrV3, manganese-phosphated
- Explanation of the article number: 31 KR 16-32 = ratchet 31 K 16" and insert ring 31 R 32 mm

### Article information

Contents (Qty of pieces)	1	Head height 1 [mm]	31,5 mm
Net weight [kg]	2,302 kg	Width of head 1 [mm]	78,1 mm
Total length [mm]	635 mm	Total length [inch]	25
Surface	manganese phosphated	Ring profile	UNIT-DRIVE
Material	Chrome-vanadium steel 31CrV3	Insert ring double hexagon	46