

AR-AR-040-1C2

Thermoelectric assembly, air to air, 12Vdc, 21 watts, no cold fan

Features

Intricate control over temperature,
Compact design, DC operation

Applications

Electronics' cabinets, Medical instrumentation, Analytical diagnostics, Industrial automation, Food and beverage cooling, Laser systems' cooling.



Physical Properties	Value
Max cooling power (W)	40
Nominal voltage (V)	18
Nominal current (A)	3.8
Power input (W)	75
Dimensions (mm)	208 x 162 x 102
Weight (kg)	1.2
Fan speed (RPM)	2000
Noise (DbA)	40
NTC sensor included	Yes

AR-AR-040-1C2

Thermoelectric assembly, air to air, 12Vdc, 21 watts, no cold fan

